

## **DL-DA12 Installation Guide**

HDMI Distribution Amplifier Rev 140624

The Digitalinx DL-DA12 is a one input to two output HDMI distribution amplifier (DA). The DL-DA12 supports supports 3D and 4K video resolutions as well as multichannel audio formats. The EDID settings of the display on Output 1 are used to negotiate with the source device.



## Instructions:

- 1. Connect the source device to the HDMI input using an HDMI cable that is less than or equal to 5 meters in length. If the source device that is further away, it is highly recommended to install a Digitalinx DL-HD70 or DL-HDE100.
- 2. Connect the display devices to HDMI outputs using HDMI cables that are less than or equal to 5 meters in length. For display devices that are further away, it is highly recommended to install a Digitalinx DL-HD70 or DL-HDE100.
- 3. Plug the power supply into the power input port on the rear of the distribution amplifier. Twist the collar of the power plug in a clockwise direction to secure the connection.



Phone: 719-260-0061 Toll-Free: 800-530-8998 Fax: 719-260-0075