

CellTap

WIRELESS TELEPHONE TAP

Need to record your cell conversations? Connect CellTap between the 2.5 mm earpiece jack of your cell phone and your earpiece or headset. Now connect a tape recorder or powered speakers to the 3.5 mm mini jack. The audio jack contains a nice mix of both sides of the conversation, provided your cell phone provides adequate sidetone.

CellTap works with most wireless phones that accept a third party headset or earpiece.

Group Listen—Simply connect a powered speaker to the audio output jack and you will have a new conferencing capability. Everyone in the room can hear your conversation, but only the person wearing the headset can talk to the distant party. While this is not a speakerphone, in many cases it is more suitable for sales presentations or contract talks.




CE



Specifications

	Output	Interface Jack:	1/4" - 3 conductor (36" cable provided 1/4" - 3 conductor to 2.5 mm- 3 conductor)
	1/8" (3.5mm) Mono		
Impedance:	600 ohms	Headset Jack:	2.5 mm micro jack
Level:	100 mV RMS (-18 dBm) nom	Passive, no AC or battery power needed	
		Size:	2" x 2" x 1.3" (5.1 x 5.1 x 3.3 cm)
		Weight:	3.5 oz. (100 Grams)



JK Audio